

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Zinc Flake Cr6+ Free, Class 10.9 M24X200

Article number	04105.240.200
Brand	-
UBB	500505566090
UNSPSC	31161620
EAN	8715494440653
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	200 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ISO	4014
DIN	931
NEN	1555
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	200
P	3

Technical Drawing



