

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Plain, Class 12.9 M20X140

Article number	04108.200.140
Brand	-
UBB	955351412049
UNSPSC	31161620
EAN	8715493850002
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	140 mm
Class	12.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-112
ASME	B18.2.3.1M
NEN	1555
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	140
P	2.5
s	30

Technical Drawing

