



DIN 6921 Hexagon Flange Bolt, Plain, Class 10.9 M16X35

Article number	04132.160.035
Brand	-
UBB	954351301823
UNSPSC	31161620
EAN	8715492120229
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	35 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info	Specific features of hexagon bolts with flange:The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure.Large (oversized) holes and/or tooling holes can be covered by the flange.Washers are not necessary.
------	--

Standards

ASME	≈B18.2.3.4M
EN	≈1665
ISO	≈4162
DIN	6921

Technical Specification

b (min.)	38
----------	----

Technical Drawing

d-D	M16
dc (max.)	35
k (max.)	14.4
L (mm)	35
P	2
s	21

