



**DIN 6921 Hexagon Flange Bolt, Zinc Plated, Class 10.9 M10X40**

|                |               |
|----------------|---------------|
| Article number | 04137.100.040 |
| Brand          | -             |
| UBB            | 500648944832  |
| UNSPSC         | 31161620      |
| EAN            | 8717077238619 |
| PKG. of 100    | Full Box Only |

**Technical Parameters**

|                   |               |
|-------------------|---------------|
| Diameter          | M10           |
| Length            | 40 mm         |
| Class             | 10.9          |
| Driving features  | Hexagon       |
| Head shape        | Hexagon head  |
| Material          | Steel         |
| Thread direction  | Right         |
| Surface treatment | Zinc plated   |
| Thread            | Metric thread |

Info      Warning:  
electroplating of these products may cause hydrogen embrittlement. Specific features of hexagon bolts with flange: The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure. Large (oversized) holes and/or tooling holes can be covered by the flange. Washers are not necessary.

**Standards**

|      |             |
|------|-------------|
| EN   | ≈1665       |
| DIN  | 6921        |
| ASME | ≈B18.2.3.4M |
| ISO  | ≈4162       |

Technical Specification

|           |      |
|-----------|------|
| b (min.)  | 26   |
| d-D       | M10  |
| dc (max.) | 22.3 |
| k (max.)  | 9.2  |
| L (mm)    | 40   |
| P         | 1.5  |
| s         | 15   |

Technical Drawing

