

DIN 960 Partially Threaded Metric Fine Hexagon Head Bolt, Plain, Class 10.9 M10X1,25X60



Article number	04160.100.060
Brand	-
UBB	953351824735
UNSPSC	31161620
EAN	8715492120632
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	60 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric fine thread

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ISO	8765
NEN	1555
DIN	960
NF	E25-152

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	60
P	1.25

Technical Drawing



