

DIN 960 Partially Threaded Metric Fine Hexagon Head Bolt, Plain, Class 10.9 M30X2,00X120



Article number	04160.300.120
Brand	-
UBB	500644710682
UNSPSC	31161620
EAN	8717077019614
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M30
Length	120 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric fine thread

Info Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-152
NEN	1555
ISO	8765
DIN	960

Technical Specification

b (min.): 125mmL≤200mm	72
b (min.): L200mm	85
b (min.): L≤125mm	66
d-D	M30
k	18.7
L (mm)	120
P	2

Technical Drawing



