



Hexagon socket head cap screw fully threaded DIN ≈912 Steel Plain 12.9 M8X50

Article number	07010.080.050
Brand	-
UBB	952351501335
UNSPSC	31161605
EAN	8715492051318
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	50 mm
Class	12.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

DIN	≈912
NF	≈E25-125
NEN	≈1241
ISO	≈4762
ASME	≈B18.3.1M
BS	≈4168-1

Technical Specification

d-D	M8
dk (max.)	13
k (max.)	8
L (mm)	50
P	1.25
s	6

Technical Drawing

