



Hexagon socket head cap screw DIN 912 Steel Plain 10.9 M6X230

Article number	07015.060.230
Brand	-
UBB	500645047696
UNSPSC	31161605
EAN	8717077054400
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M6
Length	230 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NEN	1241
NF	E25-125
DIN	912
ASME	B18.3.1M
ISO	4762
BS	4168-1

Technical Specification

b	24
d-D	M6
dk (max.)	10
Full thread if $L \leq$	30
k (max.)	6
L (mm)	230
P	1
s	5

Technical Drawing

