



Hexagon socket head cap screw DIN 912 Steel Plain 10.9 M27X70

Article number	07015.270.070
Brand	-
UBB	500644760349
UNSPSC	31161605
EAN	8717077024588
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M27
Length	70 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-125
DIN	912
ISO	4762
BS	4168-1
ASME	B18.3.1M
NEN	1241

Technical Specification

b	66
d-D	M27
dk (max.)	40
Full thread if $L \leq$	90
k (max.)	27
L (mm)	70
P	3
s	19

Technical Drawing

