



Hexagon socket head cap screw DIN 912 Steel Plain 10.9 M33X100

Article number	07015.330.100
Brand	-
UBB	500644768441
UNSPSC	31161605
EAN	8717077025394
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M33
Length	100 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ISO	4762
NEN	1241
BS	4168-1
ASME	B18.3.1M
DIN	912
NF	E25-125

Technical Specification

b	78
d-D	M33
dk (max.)	50
Full thread if $L \leq$	100
k (max.)	33
L (mm)	100
P	3.5
s	24

Technical Drawing

