



Hexagon socket head cap screw DIN 912 Steel Plain 10.9 M36X80

Article number	07015.360.080
Brand	-
UBB	500644771155
UNSPSC	31161605
EAN	8717077025660
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M36
Length	80 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

DIN	912
ASME	B18.3.1M
NF	E25-125
NEN	1241
BS	4168-1
ISO	4762

Technical Specification

b	84
d-D	M36
dk (max.)	54
Full thread if $L \leq$	110
k (max.)	36
L (mm)	80
P	4
s	27

Technical Drawing

