



Hexagon socket head cap screw DIN 912 Steel Plain 10.9 M36X180

Article number	07015.360.180
Brand	-
UBB	500644772062
UNSPSC	31161605
EAN	8717077025752
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M36
Length	180 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NEN	1241
ASME	B18.3.1M
NF	E25-125
BS	4168-1
ISO	4762
DIN	912

Technical Specification

b	84
d-D	M36
dk (max.)	54
Full thread if $L \leq$	110
k (max.)	36
L (mm)	180
P	4
s	27

Technical Drawing

