

Hexagon socket head cap screw DIN 912 Steel Plain 10.9 M36X190



Article number 07015.360.190

Brand -

UBB 500644772146

UNSPSC 31161605

EAN 8717077025769

PKG. of 1 Full Box Only

Technical Parameters

Diameter (d-D)	M36
Length (L) (mm)	190
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
 Warning:
 electroplating of
 these products may
 cause hydrogen
 embrittlement.

Standards

BS	4168-1
ASME	B18.3.1M
DIN	912
ISO	4762
NF	E25-125

Technical Specification

b	84
d_k (max.)	54
Full thread if $L \leq$	110
k (max.)	36
P	4
s	27

Technical Drawing

