



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M12X70

Article number	07021.120.070
Brand	-
UBB	500647929685
UNSPSC	31161605
EAN	8717077280984
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	70 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread

Info
A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ASME	B18.3.1M
ISO	4762
NEN	1241
NF	E25-125
DIN	912
BS	4168-1

Technical Specification

b	36
d-D	M12
dk (max.)	18
Full thread if $L \leq$	50
k (max.)	12
L (mm)	70
P	1.75
s	10

Technical Drawing

