



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 10.9 M12X80

Article number	07021.120.080
Brand	-
UBB	500647929842
UNSPSC	31161605
EAN	8717077281004
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	80 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread

Info
A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

NEN	1241
ISO	4762
DIN	912
NF	E25-125
BS	4168-1
ASME	B18.3.1M

Technical Specification

b	36
d-D	M12
dk (max.)	18
Full thread if $L \leq$	50
k (max.)	12
L (mm)	80
P	1.75
s	10

Technical Drawing

