



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M3X12

Article number	07023.030.012
Brand	-
UBB	500647934461
UNSPSC	31161605
EAN	8717077281462
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	12 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

NF	E25-125
ISO	4762
BS	4168-1
NEN	1241
ASME	B18.3.1M
DIN	912

Technical Specification

b	18
d-D	M3
dk (max.)	5.5
Full thread if $L \leq$	20
k (max.)	3
L (mm)	12
P	0.5
s	2.5

Technical Drawing

