



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M5X55

Article number	07023.050.055
Brand	-
UBB	500647937928
UNSPSC	31161605
EAN	8717077281813
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	55 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

ISO	4762
NF	E25-125
DIN	912
NEN	1241
BS	4168-1
ASME	B18.3.1M

Technical Specification

b	22
d-D	M5
dk (max.)	8.5
Full thread if $L \leq$	25
k (max.)	5
L (mm)	55
P	0.8
s	4

Technical Drawing

