



Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M14X45

Article number	07023.140.045
Brand	-
UBB	500647952844
UNSPSC	31161605
EAN	8717077283305
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	45 mm
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

BS	4168-1
ISO	4762
NEN	1241
DIN	912
ASME	B18.3.1M
NF	E25-125

Technical Specification

b	40
d-D	M14
dk (max.)	21
Full thread if $L \leq$	55
k (max.)	14
L (mm)	45
P	2
s	12

Technical Drawing

