

Hexagon socket head cap screw DIN 912 Steel Zinc plated 10.9 M36X80



Article number	07023.360.080
Brand	-
UBB	500647966968
UNSPSC	31161605
EAN	8717077284715
PKG. of 1	Full Box Only

Technical Parameters

Diameter (d-D)	M36
Length (L) (mm)	80
Class	10.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
 Warning:
 electroplating of
 these products may
 cause hydrogen
 embrittlement.

Standards

ISO	4762
NF	E25-125
ASME	B18.3.1M
DIN	912
BS	4168-1

Technical Specification

b	84
d _k (max.)	54
Full thread if L ≤	110
k (max.)	36
P	4
s	27

Technical Drawing

