



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 12.9 M20X180

Article number	07025.200.180
Brand	-
UBB	500644778184
UNSPSC	31161605
EAN	8717077026360
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	180 mm
Class	12.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread

Info
A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ASME	B18.3.1M
BS	4168-1
ISO	4762
DIN	912
NEN	1241
NF	E25-125

Technical Specification

b	52
d-D	M20
dk (max.)	30
Full thread if $L \leq$	75
k (max.)	20
L (mm)	180
P	2.5
s	17

Technical Drawing

