



## Hexagon socket head cap screw with low head and pilot recess DIN 6912 Steel Plain 08.8 M4X6

Article number	07030.040.006
Brand	-
UBB	500645058735
UNSPSC	31161605
EAN	8717077046085
PKG. of 500	Full Box Only

### Technical Parameters

Diameter	M4
Length	6 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

#### Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070',

### Standards

DIN	6912
-----	------

**FABORY** or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

b (min.): $L \leq 125\text{mm}$	14
d-D	M4
dh	2
dk	7
Full thread if $L \leq$	16
k	2.8
L (mm)	6
P	0.7
s	3

## Technical Drawing

