



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 8.8 M4X40

Article number	07065.040.040
Brand	-
UBB	500577360067
UNSPSC	31161605
EAN	8715494328852
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	40 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread

Info
A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ASME	B18.3.1M
DIN	912
NF	E25-125
ISO	4762
NEN	1241
BS	4168-1

Technical Specification

b	20
d-D	M4
dk (max.)	7
Full thread if L ≤	25
k (max.)	4
L (mm)	40
P	0.7
s	3

Technical Drawing

