



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 8.8 M5X16

Article number	07065.050.016
Brand	-
UBB	500577360489
UNSPSC	31161605
EAN	8715494328890
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	16 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread

Info
A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

NEN	1241
ISO	4762
NF	E25-125
BS	4168-1
ASME	B18.3.1M
DIN	912

Technical Specification

b	22
d-D	M5
dk (max.)	8.5
Full thread if L ≤	25
k (max.)	5
L (mm)	16
P	0.8
s	4

Technical Drawing

