



Hexagon socket head cap screw DIN 912 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 8.8 M5X60

Article number	07065.050.060
Brand	-
UBB	500577361214
UNSPSC	31161605
EAN	8715494328975
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	60 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread

Info
A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

ISO	4762
ASME	B18.3.1M
DIN	912
NEN	1241
BS	4168-1
NF	E25-125

Technical Specification

b	22
d-D	M5
dk (max.)	8.5
Full thread if $L \leq$	25
k (max.)	5
L (mm)	60
P	0.8
s	4

Technical Drawing

