



**Hexagon socket head cap screw with low head DIN 7984 Steel Zinc plated 08.8 M8X100**

Article number	07090.080.100
Brand	-
UBB	500645088930
UNSPSC	31161605
EAN	8717077058774
PKG. of 100	Full Box Only

**Technical Parameters**

Diameter	M8
Length	100 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

**Info**  
Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070',

**Standards**

DIN	7984
-----	------

**FABORY** or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

b (min.)	22
d-D	M8
dk	13
Full thread if $L \leq$	30
k	5
L (mm)	100
P	1.25
s	5

## Technical Drawing

