

## Hexagon socket head shoulder screw UNC ASME B18.3 Steel Plain 012.9 (1/2)5/8X2 Inch



Article number	07116.127.050
Brand	-
UBB	953351306477
UNSPSC	31161605
EAN	8715492066794
PKG. of 5	Full Box Only

### Technical Parameters

Length	2 Inch
Class	012.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse

### Standards

BS	2470
ASME	B18.3

Info	Warning: electroplating of these products may cause hydrogen embrittlement.All dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for these screws is 3A,
------	--

plating can cause  
thread fit problems.

**FABURY**

### Technical Specification

A (max.)	0.875
D	0.625
D1	0.5
E	0.75
H (max.)	0.375
J	0.3125
Threads per inch	13
D (min.)	0.621
D (max.)	0.623

### Technical Drawing

