



**Hexagon socket head
shoulder screw UNC ASME
B18.3 Steel Plain 012.9
(5/8)3/4X3.1/2**

| | |
|----------------|---------------|
| Article number | 07116.158.088 |
| Brand | - |
| UBB | 953351307202 |
| UNSPSC | 31161605 |
| EAN | 8715492066879 |
| PKG. of 3 | Full Box Only |

Technical Parameters

| | |
|-------------------|----------------------------|
| Length | 3.1/2 Inch |
| Class | 012.9 |
| Driving features | Hexagon socket |
| Head shape | Cylindrical head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Plain |
| Thread | Unified National Coarse |

Standards

| | |
|------|-------|
| BS | 2470 |
| ASME | B18.3 |

| | |
|------|--|
| Info | Warning: electroplating of these products may cause hydrogen embrittlement.All dimensions in above table are in inches.Marking of these screws is not mandatory.Due to the unfavourable head geometry these fasteners have reduced loadability.Attention: As the thread tolerance class for these screws is 3A, |
|------|--|

plating can cause
thread fit problems.

FABURY

Technical Specification

| | |
|------------------|-------|
| A (max.) | 1 |
| D | 0.75 |
| D1 | 0.625 |
| E | 0.875 |
| H (max.) | 0.5 |
| J | 0.375 |
| Threads per inch | 11 |
| D (min.) | 0.746 |
| D (max.) | 0.748 |

Technical Drawing

