



**Hexagon socket head  
shoulder screw tolerance h8  
ISO ≈7379 Steel Plain 012.9  
(M10)12X100**

Article number	07117.100.100
Brand	-
UBB	953351822424
UNSPSC	31161605
EAN	8715492067227
PKG. of 25	Full Box Only

**Technical Parameters**

Diameter	M10
Length	100 mm
Class	012.9
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement. Due  
to the unfavourable  
head geometry  
these fasteners  
have reduced  
loadability. Steel  
fasteners with  
reduced loadability  
are marked with a  
'0' preceding the  
property class mark,  
e.g. '010.9'. Stainless  
steel fasteners with  
reduced loadability  
are either marked

**Standards**

ISO	≈7379
BS	≈4168-7
ASME	≈B18.3.3M

with a '0' preceding  
the property class  
mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

b	16
d-D	M10
dk (max.)	18.27
ds	12
ds (nom.)	12
k (max.)	9
L (mm)	100
P	1.5
s	6
Tolerance h8 (max.)	12
Tolerance h8 (min.)	11.973

## Technical Drawing

