



Hexagon socket button head screw with flange ISO 7380-2 Steel Zinc plated 010.9 M4X10

Article number	07141.040.010
Brand	-
UBB	951351888031
UNSPSC	31161518
EAN	8715492067609
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	10 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

Warning: electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked

Standards

ISO	7380-2
-----	--------

FABORY with a '0' preceding
the property class
mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technical Specification

d-D	M4
dc (max.)	9.4
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	10
P	0.7
s	2.5

Technical Drawing

