



**Hexagon socket button head screw with flange ISO 7380-2  
Steel Zinc plated 010.9 M6X8**

Article number	07141.060.008
Brand	-
UBB	951351889369
UNSPSC	31161518
EAN	8715492067791
PKG. of 200	Full Box Only

**Technical Parameters**

Diameter	M6
Length	8 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

Warning:  
electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

**Standards**

ISO	7380-2
-----	--------

**FABORY** the property class  
mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

d-D	M6
dc (max.)	13.6
Full thread if $L \leq$	30
k (max.)	3.3
L (mm)	8
P	1
s	4

## Technical Drawing

