



Hexagon socket button head screw with flange ISO 7380-2 Steel Zinc plated 010.9 M6X20

| | |
|----------------|---------------|
| Article number | 07141.060.020 |
| Brand | - |
| UBB | 951351889773 |
| UNSPSC | 31161518 |
| EAN | 8715492067838 |
| PKG. of 200 | Full Box Only |

Technical Parameters

| | |
|-------------------|----------------|
| Diameter | M6 |
| Length | 20 mm |
| Class | 010.9 |
| Driving features | Hexagon socket |
| Head shape | Button head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc plated |
| Thread | Metric thread |

Info

Warning: electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked

Standards

| | |
|-----|--------|
| ISO | 7380-2 |
|-----|--------|

FABORY with a '0' preceding
the property class
mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technical Specification

| | |
|-------------------------|------|
| d-D | M6 |
| dc (max.) | 13.6 |
| Full thread if $L \leq$ | 30 |
| k (max.) | 3.3 |
| L (mm) | 20 |
| P | 1 |
| s | 4 |

Technical Drawing

