



## Hexagon socket button head screw with flange ISO 7380-2 Steel Zinc plated 010.9 M6X20

Article number	07141.060.020
Brand	-
UBB	951351889773
UNSPSC	31161518
EAN	8715492067838
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	20

**Info**

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated

### Standards

ISO	7380-2
-----	--------

Thread

Metric thread

Info

Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement.

### Technical Specification

$d_c$ (max.)	13.6
Full thread if $L \leq$	30
$k$ (max.)	3.3
P	1
s	4

### Technical Drawing

