



Hexagon socket button head screw with flange ISO 7380-2 Steel Zinc plated 010.9 M10X16

Article number	07141.100.016
Brand	-
UBB	951351891167
UNSPSC	31161518
EAN	8715492068019
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D) M10

Length (L) (mm) 16

Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Class 010.9

Driving features Hexagon socket

Head shape Button head

Material Steel

Thread direction Right

Surface treatment Zinc plated

Standards

ISO 7380-2

Thread

Metric thread

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Technical Specification

d_c (max.)	21.9
Full thread if $L \leq$	40
k (max.)	5.5
P	1.50
s	6

Technical Drawing

