



Hexagon socket button head screw ISO 7380-1 Steel Plain 010.9 M3X30

Article number	07150.030.030
Brand	-
UBB	953351992128
UNSPSC	31161518
EAN	8715492068552
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	30 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:
electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

Standards

ISO	7380-1
ASME	≈B18.3.4M
BS	≈4168-6
NF	≈E25-126

FABORY the property class
mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technical Specification

d-D	M3
dk (max.)	5.7
Full thread if $L \leq$	20
k (max.)	1.65
L (mm)	30
P	0.5
s	2

Technical Drawing

