



**Hexagon socket button head screw ISO 7380-1 Steel Plain 010.9 M6X6**

Article number	07150.060.006
Brand	-
UBB	950351438250
UNSPSC	31161518
EAN	8715492068866
PKG. of 200	Full Box Only

**Technical Parameters**

Diameter	M6
Length	6 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Button head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:  
electroplating of these products may cause hydrogen embrittlement. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

**Standards**

NF	≈E25-126
ISO	7380-1
ASME	≈B18.3.4M
BS	≈4168-6

**FABORY** the property class  
mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

d-D	M6
dk (max.)	10.5
Full thread if $L \leq$	30
k (max.)	3.3
L (mm)	6
P	1
s	4

## Technical Drawing

