



## Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M4X22

|                |               |
|----------------|---------------|
| Article number | 07160.040.022 |
| Brand          | -             |
| UBB            | 500645093476  |
| UNSPSC         | 31161605      |
| EAN            | 8717077059221 |
| PKG. of 500    | Full Box Only |

### Technical Parameters

|                   |                  |
|-------------------|------------------|
| Diameter          | M4               |
| Length            | 22 mm            |
| Class             | 8.8              |
| Driving features  | Hexagon socket   |
| Head shape        | Cylindrical head |
| Material          | Steel            |
| Thread direction  | Right            |
| Surface treatment | Zinc plated      |
| Thread            | Metric thread    |

### Standards

|      |          |
|------|----------|
| BS   | 4168-1   |
| NEN  | 1241     |
| ASME | B18.3.1M |
| DIN  | 912      |
| ISO  | 4762     |
| NF   | E25-125  |

### Technical Specification

|                         |     |
|-------------------------|-----|
| b                       | 20  |
| d-D                     | M4  |
| dk (max.)               | 7   |
| Full thread if $L \leq$ | 25  |
| k (max.)                | 4   |
| L (mm)                  | 22  |
| P                       | 0.7 |
| s                       | 3   |

### Technical Drawing

