



Hexagon socket head cap screw DIN 912 Steel Zinc plated 8.8 M5X65

Article number	07160.050.065
Brand	-
UBB	500645094953
UNSPSC	31161605
EAN	8717077059375
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	65 mm
Class	8.8
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	1241
ASME	B18.3.1M
BS	4168-1
DIN	912
ISO	4762
NF	E25-125

Technical Specification

b	22
d-D	M5
dk (max.)	8.5
Full thread if $L \leq$	25
k (max.)	5
L (mm)	65
P	0.8
s	4

Technical Drawing

