



## Hexagon socket countersunk head screw ISO 10642 Steel Plain 010.9 M18X100

Article number	07400.180.100
Brand	-
UBB	952351364478
UNSPSC	31161518
EAN	8715492084224
PKG. of 25	Full Box Only

### Technical Parameters

Diameter	M18
Length	100 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

#### Info

Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement.All  
thread lengths  
are guide values  
only and may  
deviate.Due to  
the unfavourable  
head geometry  
these fasteners  
have reduced  
loadability.Steel  
fasteners with  
reduced loadability  
are marked with a  
'0' preceding the  
property class mark,

### Standards

DIN	≈7991
ISO	10642

e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

## Technical Specification

b (min.)	42
d-D	M18
dk (max.)	33
Full thread if $L \leq$	60
k (max.)	8
L (mm)	100
P	2.5
s	12
$\alpha$	90

## Technical Drawing

