



**Hexagon socket  
countersunk head screw  
ISO 10642 Steel Plain 010.9  
M24X70**

Article number	07400.240.070
Brand	-
UBB	950351484775
UNSPSC	31161518
EAN	8715492084576
PKG. of 10	Full Box Only

**Technical Parameters**

Diameter	M24
Length	70 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement.All  
thread lengths  
are guide values  
only and may  
deviate.Due to  
the unfavourable  
head geometry  
these fasteners  
have reduced  
loadability.Steel  
fasteners with  
reduced loadability  
are marked with a  
'0' preceding the  
property class mark,

**Standards**

ISO	10642
DIN	≈7991

e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

## Technical Specification

b (min.)	54
d-D	M24
dk (max.)	39
Full thread if $L \leq$	90
k (max.)	14
L (mm)	70
P	3
s	14
$\alpha$	60

## Technical Drawing

