



**Hexagon socket
countersunk head screw
ISO 10642 Steel Plain 010.9
M24X180**

Article number	07400.240.180
Brand	-
UBB	952351055746
UNSPSC	31161518
EAN	8715492084668
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	180 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info	Warning: electroplating of these products may cause hydrogen embrittlement.All thread lengths are guide values only and may deviate.Due to the unfavourable head geometry these fasteners have reduced loadability.Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark,
------	--

Standards

DIN	≈7991
ISO	10642

e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Technical Specification

b (min.)	54
d-D	M24
dk (max.)	39
Full thread if $L \leq$	90
k (max.)	14
L (mm)	180
P	3
s	14
α	60

Technical Drawing

