



## Hexagon socket countersunk head screw ISO ≈10642 Steel Dacromet 500 LC Grade A 010.9 M8X16

Article number	07403.080.016
Brand	-
UBB	952351665353
UNSPSC	31161518
EAN	8715492150028
PKG. of 200	Full Box Only

### Technical Parameters

Diameter	M8
Length	16 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Dacromet 500 LC Grade A
Thread	Metric thread

#### Info

All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked

### Standards

DIN	≈7991
ISO	≈10642
NEN	≈2359
BS	≈4168-8

**FABORY** with a '0' preceding  
the property class  
mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

b (min.)	28
d-D	M8
dk (max.)	16.43
Full thread if $L \leq$	45
k (max.)	4.96
L (mm)	16
P	1.25
s	5
$\alpha$	90

## Technical Drawing

