



**Hexagon socket
countersunk head screw
ISO 10642 Steel Zinc flake
Cr6+free - ISO 10683 flZnnc
010.9 M8X40**

Article number	07407.080.040
Brand	-
UBB	500571181220
UNSPSC	31161518
EAN	8715494143073
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	40 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread

Info

A zinc flake coating eliminates the risk of hydrogen embrittlement. All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a

Standards

ISO	10642
DIN	≈7991

'0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Technical Specification

b (min.)	28
d-D	M8
dk (max.)	16.43
Full thread if $L \leq$	45
k (max.)	4.96
L (mm)	40
P	1.25
s	5
α	90

Technical Drawing

