



Hexagon socket countersunk head screw ISO 10642 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 010.9 M10X25

Article number	07407.100.025
Brand	-
UBB	500571181485
UNSPSC	31161518
EAN	8715494143097
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M10
Length	25 mm
Class	010.9
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread

Info

A zinc flake coating eliminates the risk of hydrogen embrittlement. All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a

Standards

DIN	≈7991
ISO	10642

'0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Technical Specification

b (min.)	32
d-D	M10
dk (max.)	20.69
Full thread if $L \leq$	50
k (max.)	6.2
L (mm)	25
P	1.5
s	6
α	90

Technical Drawing

