



## Hexalobular socket countersunk head screw ISO ≈10642 Steel Zinc plated 08.8 M5X30

Article number	07450.050.030
Brand	-
UBB	500504777151
UNSPSC	31161518
EAN	8715494195935
PKG. of 200	Full Box Only

### Technical Parameters

Diameter	M5
Length	30 mm
Class	08.8
Driving features	Hexalobular
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

#### Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070',

### Standards

ISO	≈10642
DIN	≈7991

**FABORY** or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

b (min.)	16
d-D	M5
dk	10
k (max.)	2.8
L (mm)	30
P	0.8
Socket	25
$\alpha$	90

## Technical Drawing

