



Hexalobular socket countersunk head screw ISO ≈10642 Steel Zinc plated 08.8 M6X30

Article number	07450.060.030
Brand	-
UBB	954351376908
UNSPSC	31161518
EAN	8715492150936
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	30 mm
Class	08.8
Driving features	Hexalobular
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070',

Standards

ISO	≈10642
DIN	≈7991

FABORY or with the steel
grade only, e.g. 'A2'.

Technical Specification

b (min.)	18
d-D	M6
dk	12
k (max.)	3.3
L (mm)	30
P	1
Socket	30
α	90

Technical Drawing

