



Hexalobular socket countersunk head screw ISO ≈10642 Steel Zinc plated 08.8 M8X35

Article number	07450.080.035
Brand	-
UBB	500504717421
UNSPSC	31161518
EAN	8715494195980
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	35 mm
Class	08.8
Driving features	Hexalobular
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070',

Standards

ISO	≈10642
DIN	≈7991

FABORY or with the steel
grade only, e.g. 'A2'.

Technical Specification

b (min.)	22
d-D	M8
dk	16
k (max.)	4.4
L (mm)	35
P	1.25
Socket	40
α	90

Technical Drawing

