



Hexagon socket countersunk head screw ISO 10642 Steel Zinc plated 8.8 M3X8

Article number	07470.030.008
Brand	-
UBB	950351485764
UNSPSC	31161518
EAN	8715492150998
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	8 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

Standards

DIN	≈7991
ISO	10642

FABORY the property class
mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technical Specification

b (min.)	18
d-D	M3
dk (max.)	5.81
Full thread if $L \leq$	25
k (max.)	1.86
L (mm)	8
P	0.5
s	2
α	90

Technical Drawing

