



## Hexagon socket countersunk head screw ISO 10642 Steel Zinc plated 8.8 M3X25

Article number	07470.030.025
Brand	-
UBB	950351486267
UNSPSC	31161518
EAN	8715492151056
PKG. of 200	Full Box Only

### Technical Parameters

Diameter	M3
Length	25 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

#### Info

All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

### Standards

ISO	10642
DIN	≈7991

**FABORY** the property class  
mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

b (min.)	18
d-D	M3
dk (max.)	5.81
Full thread if $L \leq$	25
k (max.)	1.86
L (mm)	25
P	0.5
s	2
$\alpha$	90

## Technical Drawing

