



Hexagon socket countersunk head screw ISO 10642 Steel Zinc plated 8.8 M4X50

Article number	07470.040.050
Brand	-
UBB	950351953878
UNSPSC	31161518
EAN	8715492151193
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	50 mm
Class	08.8
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding

Standards

ISO	10642
DIN	≈7991

FABORY the property class
mark, e.g. 'A2-070',
or with the steel
grade only, e.g. 'A2'.

Technical Specification

b (min.)	20
d-D	M4
dk (max.)	7.96
Full thread if $L \leq$	25
k (max.)	2.48
L (mm)	50
P	0.7
s	2.5
α	90

Technical Drawing

