



Hexagon head bolt with hexagon nut DIN 601/555 Steel Plain 4.6 M10X60

Article number	08000.100.060
Brand	-
UBB	500648010337
UNSPSC	31161620
EAN	8717077272514
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	60 mm
Class	4.6
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	The property class of the corresponding nuts is 4 as a minimum.

Standards

ISO	≈4016/4033
NEN	102/697
DIN	601/555
NF	E25-115-1/E25-402

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	60
m	8
P	1.5
s	17

Technical Drawing

